

This is a dedicated bracket for securing the TH2/TH Series Light Units. You can secure the Light Units at four points.

Model name	Applicable Light Unit (Common for all colors)]	 Dimensions (mm) BK-TH-LE12 	
BK-TH-LE12	For the TH2/TH series		DR-TH-LE IZ	5 5
	ket is not applicable to the camera-windo 00 mm emitting surface and to the large t			12 22 22 22 22 22 22 22
				۱

Brackets Options

PD3 series PD2 series

STU-3000

PSB series

POD series

PTU2 series

PF-A4048-2

PB-2430-1 CC-ST-1024

BB series

PJ series

PSCC

CC-PJ-0707

PSB3-30024

Lens Filters

Diffusion Plates

Polarizing Plates

Light Control Films

Extension Cables

277

Brackets

Other


Units

Control (

You can combine Dome and Ring Lights. Imaging can be performed by lighting switching or simultaneous lighting.

Model name Applicable Light Unit 1 (Common for all colors) Dimensions A B C Thick BK-75-JO HPD2-75 series LDR2-100-LA series 84 91 35 BK-100-JO HPD2-100 series LDR2-100-LA series 106 116 32 BK-150-JO HPD2-150 series LDR2-100-LA series 106 116 32 BK-150-JO HPD2-150 series LDR2-160-LA series 106 116 32 BK-150-JO HPD2-150 series LDR2-170-LA series 140 166 42	kness
BK-75-JO HPD2-75 series LDR2-100-LA series 84 91 35 BK-100-JO HPD2-100 series HPR2-100 series 106 116 32 BK-100-JO HPD2-100 series LDR2-132-LA series 106 116 32 BK-150-JO HPD2-150 series LDR2-160-LA series 106 116 32 BK-150-JO HPD2-150 series LDR2-170-LA series 140 166 42	
LDR-96-LA1 series I I BK-100-JO HPD2-100 series LDR-132-LA series 106 116 32 BK-150-JO HPD2-150 series LDR-146-LA1 series 106 116 32 BK-150-JO HPD2-150 series LDR2-170-LA series 140 166 42	
BK-100-JO HPD2-100 series HPR2-100 series 106 116 32 BK-100-JO HPD2-100 series LDR2-132-LA series 106 116 32 BK-150-JO HPD2-150 series LDR2-170-LA series 140 166 42	
BK-100-JO HPD2-100 series LDR2-132-LA series 106 116 32 LDR-146-LA1 series HPR2-150 series 106 116 32 BK-150-JO HPD2-150 series LDR2-170-LA series 140 166 42	
BK-150-JO HPD2-150 series LDR-146-LA1 series HPR2-150 seri	
HPR2-150 series LDR2-170-LA series 140 166 42	
BK-150-JO HPD2-150 series LDR2-170-LA series 140 166 42	
	1 4
LDR-1/6-LA1 series	
HPR2-200 series	
BK-200-JO HPD2-200 series LDR2-208-LA series 170 216 52	
LDR-206-LA1 series	
BK-250-JO HPD2-250 series HPR2-250 series 210 266 56	

📄 Light joint brackets 🔥



(Four brackets are included.)

Options **Brackets**



Coaxial Light joint bracket

Expansion mounting bracket

Coaxial Light joint brackets


You can combine Dome and Coaxial Lights. Uniform illumination can be provided from all directions. Irregular illuminating is eliminated.

Ø

Model name	Applicable Light Unit 1	Applicable Light Unit 2	Dimensions		
wodername	(Common for all colors)	(Common for all colors)	A	В	С
BK-HPD2-75-LFV	HPD2-75 series	LFV3-35 series	95	66	33
BK-HPD2-100-LFV	HPD2-100 series	LFV3-50 series	113	84	45.5
BK-HPD2-150-LFV	HPD2-150 series		129.5	119	70.5
BK-HPD2-200-LFV	HPD2-200 series	LFV3-70 series	164	155	95.5
BK-HPD2-250-LFV	HPD2-250 series		200	190	116.5

 Dimensions (mm) BK-HPD2-75-LFV

BK-HPD2-100-LFV BK-HPD2-150-LFV BK-HPD2-200-LFV BK-HPD2-250-LFV




Expansion mounting brackets

These brackets are for expanding the mounting methods of Light Units. You can mount on horizontal as well as vertical surfaces.

Madal nome	Applicable Light Unit 1 (Common for all colors)	Dimensions			
Model name		A	В	С	D
BK-50-CI	HPR2-50 series	40	50	13	5
BK-75-CI	HPD2-75 series	70	91	22	
	HPR2-75 series		91		6
BK-100-CI	HPD2-100 series		116	25	
	HPR2-100 series	90			
BK-150-CI	HPD2-150 series	122 1	166	33	
	HPR2-150 series		100		
BK-200-CI	HPD2-200 series	160	216	40	
	HPR2-200 series				
BK-250-CI	HPD2-250 series	210	266	60	
	HPR2-250 series				

Dimensions (mm)





(With Light Unit installed)

• Example of the expansion mounting bracket in use

Refer to our website for product details.

Search

CCS brackets

For quick access.

You can also use

your smartphone or cell phone.



Ring Light: Image of usage with the HPR2-200RD

• Example of the expansion mounting bracket in use



Dome Light: Image of usage with the HPD2-250SW

otions

P