

1. Model

FL-CC3524-5MX


Vision Light Tech
 creating optical solutions

2. Application

For 2/3 Format Camera

3. Specification

3-1. Physical (As per the attached drawing)

- | | |
|-----------------------|---|
| (1) Dimensions | $\phi 33.0 \text{ mm} \times 65.5 \text{ mm}$ |
| (2) Weight | 100 g |
| (3) Mount | C-Mount (1 – 32 UN – 2A) |
| (4) Filter Screw Size | M30.5 mm , P = 0.5 mm |

3-2. Optical

- | | |
|-------------------------|--|
| (1) Focal Length | 35 mm $\pm 5\%$ |
| (2) Max. Aperture Ratio | 1: 2.4 |
| (3) Iris Range | F / 2.4 to F /16 |
| (4) Angle of View | Diagonal 17.8°
Horizontal 14.3°
Vertical 10.8° |
| (5) Picture format | 8.8 mm \times 6.6 mm |
| (6) Focusing Range | Inf. to 0.1 m |
| (7) Back Focal Length | 14.35mm (in air) |
| (8) Flange Back Length | 17.526 mm \pm 0.05 mm (in air) |

3-3. Mechanical

(1) Focusing Mechanism

- | | |
|--|---------------------|
| Rotation Angle | 158° |
| Rotation Torque | 1.0N·cm to 9.0 N·cm |
| Focus Ring can be fixed at any positions by
3 fixing screws or 1 thumb screw (refer to external view) | |

(2) Iris Mechanism

- | | |
|---|----------------------|
| Non-click | |
| Rotation Angle | 71.5° |
| Rotation Torque | 0.01N·cm to 5.0 N·cm |
| Iris Ring can be fixed at any positions by 3 fixing screws
or 1 thumb screw (refer to external view) | |

3-4. Vibration & Shock Test Standard

(1) Vibration Conditions

Wave	Sine Wave
Acceleration	1.96 m/s ² to 59.78 m/s ²
Cycle Range	10 Hz to 55 Hz
Cycle Period	3 Minutes
Duration of Vibration	120 Minutes Respectively in Three Dimensional Directions

(2) Shock Conditions

Tester	Shock Testing Machine by Dropping
Impact Force	588 m/s ²
Duration of Shock	3.5 ms
Directions & Number of Times	1 Time Respectively in Three Dimensional Directions

SPEC. INFO	FL—CC3524—5MX	
		July. 16. 2019

3-5. Environmental Temperature Range -10°C to $+50^{\circ}\text{C}$

4. Accessories



(1) Front Lens Cap	1 piece	
(2) Rear Lens Cap	1 piece	
(3) Fixing Screw for Focus ,Iris Ring	6 pieces	
(4) Thumbscrew for Focus ,Iris Ring	2 pieces	(for Optional Usage)
(5) Packing Box	1 pieces	

Vision Light Tech B.V.

Protonenlaan 22, 5405 NE UDEN, P.O. Box 345, 5400 AH UDEN, The Netherlands

Phone: +31 (0)413 26 00 67, Fax +31 (0)413 26 09 38, E-mail: inquiry@vlt.nl, Website: www.vlt.nl

Trade register No. 17150044, VAT No. NL8112.30.946.B01



SPEC.INFO	FL-CC3524-5MX
	July.01.2019

Vision Light Tech B.V.

Protonenlaan 22, 5405 NE UDEN, P.O. Box 345, 5400 AH UDEN, The Netherlands

Phone: +31 (0)413 26 00 67, Fax +31 (0)413 26 09 38, E-mail: inquiry@vlt.nl, Website: www.vlt.nl

Trade register No. 17150044, VAT No. NL8112.30.946.B01